


Corona-Plus

OPTIONS



Advanced technology optimises production of film, foil and paper

The Vetaphone corona stations can easily have one or more of the following options incorporated to give maximum productivity.

Robust constructions ensure absolute physical stability of the corona stations, so the wider range of stations now meets the high specifications of pullstations.

The overall measurements of the stations remained practically unchanged, leaving them just as easily to install in-line as always.

Quick Opening system - Automatic electrode retracting at high speeds minimises the non-treated area by flying splices to an absolute minimum.

NIP-roller prevents backside treatment and ensures perfect drive in pull stations. NIP pressure is controlled pneumatically at the operator panel.

Motor Drive can be synchronised or tendencies for trouble free web transport through the station.

Extended shaft for external drive system. Meets the specification for pull-stations.

Calibrated Electrode Air Gap Adjustment with digital read out ensures precise and uniform treatment of wide webs.



Fabriksvej 11, 6000 Kolding, Denmark
Tel +45 76300333 - Fax +45 76300334
www.vetaphone.com - sales@vetaphone.com